

# Stock Heavy-Duty Conveyor Pulleys

## Face

- C Crown
- F Flat

**C**

**S**

**D**

**120**

**26**

**X25**

**L**

**3**

**H**

**Lagging Style** if no letter, Lagging is Smooth

- H Herringbone
- D Diamond Groove
- C Ceramic (no thickness specified)
- S Slide Lagging
- R Radial/Circumferential
- P Parallel (with shaft)

## Pulley Type

- S Standard Duty
- M Mine Duty
- Q Quarry Duty
- QAR Quarry Duty AR

## Pulley Style

- D Drum
- W Wing

## Diameter 3 digits

**120** 12.0"

## Face Width 2 digits

**26** 26"

**Lagging Thickness** in 8th, 1 digit

**3** 3/8"

**Lagging** add "L" if lagged

**Bushing Part Number** Conveyor pulleys use "short" bushings

- XT MXT-STL (Steel)
- X MXT (Cast)
- SF, E... QD Bushing
- K TB Bushing
- H M-HE